




HI-LO ADJUSTER

Hi - Lo is regulated using a gas spring



CASTOR

Uses 2 pcs 2" swivel castors and 2 swivel wheels. Produces smooth movement when moved.




FLAT BASE

Can be applied under low beds.

SPECIFICATIONS	
Construction	Made from quality steel pipes and sheets, processed with the latest manufacturing technology.
Frame	Aluminium profile.
Table	ABS.
Hi - Lo	Can be adjusted using a gas spring
Castor	2 pcs castors 2" swivel, 2 pcs wheels.
Finishing	Epoxy powder coating finish.
Max. Load	20 kg (5 kg at the end of the table).
Net Weight	± 14 kg.
Dimensions	± (L) 810 x (W) 500 x (H) 775 - 1050 mm (overall). ± (L) 810 x (W) 450 (table).

Specifications subject to change without prior notice

DIMENSIONS (mm) ±



Eff. Date 28-08-2024

