


CELEBES ELECTRIC BED


4 MOTOR

74106



SAFETY SIDE GUARD

Full side guard panel height's 275mm from the mattress ensures protecting against patient falls. Further side guard gap protects against patient's finger pinch as well according to IEC 60601-2-52.



SIDE GUARD GAP

Celebes side guards have been specially designed in compliance with IEC 60601-2-52 to prevent entrapment risk



AUTO REGRESS

The Auto Regress System reduce pressure in patient's pelvic area when the back-raise is raised.




MATTRESS PLATFORM

Made of strong and lightweight material. Easy to clean.

SPECIFICATIONS

Construction	Made from steel pipes and steel sheets processed with the latest manufacturing technology.
Dasaran matras	Polypropylene, strong and light, easy to remove and install for cleaning.
Head & Foot Panel	Made from polypropylene, strong and light, easy to remove and install for maintenance and cleaning.
Side Guard	Polypropylene material, easy to operate (open and close), equipped with lock and inclinometer.
Positions	<ul style="list-style-type: none"> - Hi-lo mattress platform 370 - 720 mm. - Backrest inclination 0 - 70°. - Kneerest inclination 0 - 25°. - Trendelenburg - anti trendelenburg inclination -13° - 13°. Driven by 24V DC motor actuator.
Castor	4 castor 5" double wheels, equipped with central locking.
Power Suppl	100-240v, 50-60Hz, 200W.
Accessories	Inclinometer backrest, inclinometer trendelenburg/anti trendelenburg, accessories railing, stainless steel IV pole.
Finishing	Epoxy powder coating.
Max. Patient Load	185 kg.
SWL	250 kg.
Net Weight	± 138 kg.
Dimensions	± (L) 2200 x (W) 1060 x (H) 755 - 1105 mm (overall). ± (L) 1975 x (W) 900 x (H) 370 - 720 mm (on mattress platform).

DIMENSIONS (mm) ±



Specifications subject to change without prior notice

Eff. Date 30-04-2024



Marketing Office :
 Gran Rubina Business Park Lt. 22C. Komp. Rasuna Epicentrum, Jl. HR Rasuna Said - Jakarta 12940
 Ph. +62-21-837 00 555. Fax. +62-21-837 00 355, Email: mak@cbn.net.id/marketing@mak-techno.com
 www.mak-techno.com