

ELECTRIC EMERGENCY STRETCHER

31217



0-70°



0-25°




630-890mm



at. tre. 0-15°



tre. 0-15°



COLUMN MOTOR

Electrical system for Hi-Lo adjustment



5th WHEEL

Equipped with 5th wheels for more stable mobility



SIDE GUARD

Adjustable sideguard for easy access is equipped with an angle indicator to determine the tilt of the patient's back support.




X-RAY CASSETTE HOLDER

Provided holder for use of X-Ray cassette

SPECIFICATION	
Construction	High quality steel sections construction utilizing the latest manufacturing techniques throughout.
Mattress Platform	Made of materials that can be used for x-ray covered with high quality steel frame.
Positions	<ul style="list-style-type: none"> • Hi-Lo elevation: \pm 630(Lo) - 890(Hi) mm adjustable by handset • Trendelenburg - Anti trendelenburg inclination : \pm -15° - 15° adjustable by handset (electrically) • Back-raise inclination: \pm 0 - 70° gas spring mechanism. • Knee-raise inclination: \pm 0 - 25° crank mechanism.
Side Guard	Made of polypropylene material. Repositionable and equipped with lock
Upholstery	Manufactured in line using high quality foam, covered with synthetic leather.
Castor	Four 8" single wheel castor, with central lock system. Equipped with 5 th wheel system, for use ease of mobility.
Accessories	<ul style="list-style-type: none"> - X-Ray cassette holder and all under mattress platform. - Oxygen cylinder holder. - Patient seatbelts. - IV pole.
Coating	Epoxy powder coating.
Max. Patient Weight	170 kg.
Safe Working Load	200 kg.
Net Weight (approx.)	135 kg.
Dimension (\pm)	\pm (L) 2145 x (W) 795 x (H) 920 mm - 1180 mm (overall). \pm (L) 1930 x (W) 655 x (H) 630 mm - 890 mm (on mattress platform).

DIMENSION (mm) \pm :



Product images are for illustrative purposes only and color may differ from the actual product.

Eff. Date 21-11-2023



Marketing Office :
 Gran Rubina Business Park Lt. 22C. Komp. Rasuna Epicentrum, Jl. HR Rasuna Said - Jakarta 12940
 Ph. +62-21-837 00 555. Fax. +62-21-837 00 355, Email: mak@cbn.net.id/marketing@mak-techno.com
 www.mak-techno.com