




## HI-LO ADJUSTER

Hi - Lo is regulated using a gas spring



## CASTOR

Uses 2 pcs 2" swivel castors and 2 swivel wheels. Produces smooth movement when moved.



## FLAT BASE


Can be applied under low beds.

## SPECIFICATIONS

<b>Construction</b>	Made from quality steel pipes and sheets, processed with the latest manufacturing technology.
<b>Frame</b>	Aluminium profile.
<b>Table</b>	ABS.
<b>Hi - Lo</b>	Can be adjusted using a gas spring
<b>Castor</b>	2 pcs castors 2" swivel, 2 pcs wheels.
<b>Finishing</b>	Epoxy powder coating finish.
<b>Max. Load</b>	20 kg (5 kg at the end of the table).
<b>Net Weight</b>	± 14 kg.
<b>Dimensions</b>	± (L) 810 x (W) 500 x (H) 770 - 1040 mm (overall). ± (L) 810 x (W) 450 (table).

Specifications subject to change without prior notice

## DIMENSIONS (mm) ±



Eff. Date 05-03-2025



**Marketing Office :**  
 Gran Rubina Business Park Lt. 22C. Komp. Rasuna Epicentrum, Jl. HR Rasuna Said - Jakarta 12940  
 Ph. +62-21-837 00 555. Fax. +62-21-837 00 355, Email: mak@cbn.net.id/marketing@mak-techno.com  
 www.mak-techno.com